


Manifold MHA1-P2-2-M3-PI

Part number: 197227

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. number of valve positions	2
Operating pressure	0 bar ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Mounting method for sub-base	With through-hole
Mounting method for valve	Via female thread
Pneumatic connection, port 1	M7
Pneumatic connection, port 2	M3
Material sub-base	Wrought aluminium alloy