


Manifold block MHP1-PR6-3-PI-PCB

Part number: 197244

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. number of valve positions	6
Operating pressure	0 bar ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 40 °C
Mounting method for valve	Via female thread
Pneumatic connection, port 1	M5
Pneumatic connection, port 3	M5
Material sub-base	Wrought aluminium alloy