

Manifold MHA2-PR10-3-M5

Part number: 197451

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---------------------------------|----------------------------------|
| Max. number of valve positions | 10 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Mounting method for sub-base | With through-hole With H-rail |
| Mounting method for valve | Via female thread |
| Pneumatic connection, port 1/33 | M7 |
| Pneumatic connection, port 2 | M5 |
| Pneumatic connection, port 3/11 | M7 |
| Material sub-base | Wrought aluminium alloy |