

# Spiral plastic tubing PUN-4X0,75-S-0,5-SW

Part number: 197602

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                  | Value  |
|--|--|
| Working length                           | 0.5 m  |
| Outside diameter                         | 4 mm   |
| Block length                             | 0.184 m  |
| Inside diameter                          | 2.6 mm   |
| Winding diameter                         | 25 mm  |
| Number of turns                          | 20   |
| Temperature-dependent operating pressure | -0.095 MPa ... 1 MPa   |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar   |
| Temperature-dependent operating pressure | -13.775 psi ... 145 psi  |
| Approval                                 | German Technical Control Board (TÜV)   |
| Certificate issuing authority            | B 013277 0527 00   |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:-:-]  |
| LABS (PWIS) conformity                   | VDMA24364-B2-L   |
| Ambient temperature                      | -35 °C ... 60 °C   |
| Product weight                           | 13 g   |
| Pneumatic connection                     | For push-in connector O.D. 4 mm<br>For barbed fitting I.D. 3 mm with union nut<br>For barbed fitting I.D. 3 mm |
| Colour                                   | Black  |
| Shore hardness                           | D 52 +/-3  |
| Material tubing                          | TPE-U(PU)  |