

Union nut MCK-PK-3

Part number: 205254

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	Female thread M6x0.75
Operating pressure complete temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Operating pressure complete temperature range	-13.775 psi ... 174 psi
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection, port 1	For tubing outer diameter of 4 mm For barbed fitting I.D. 3 mm with union nut
Material union nut	Wrought aluminium alloy, anodised
Note on materials	RoHS-compliant