

# Clevis foot LBG-40-R3

Part number: 2078792

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40
Mounting position	optional
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	1.5 kN
Product weight	300 g
Note on materials	RoHS-compliant
Material mounting	High-alloy stainless steel
Material bolt	High-alloy stainless steel
Material lock	High-alloy stainless steel