

Union nut MCK-PK-4-KU

Part number: 211291

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	Female thread M10x1
Operating pressure complete temperature range	0 MPa ... 1 MPa
Operating pressure complete temperature range	0 bar ... 10 bar
Operating pressure complete temperature range	0 psi ... 145 psi
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection, port 1	For tubing outside diameter of 6 mm For barbed fitting I.D. 4 mm with union nut
Material union nut	POM
Note on materials	RoHS-compliant