

Quick coupling socket KD4-1/4-A

Part number: 2143

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal size	8 mm
Operating pressure complete temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Operating pressure complete temperature range	-13.775 psi ... 174 psi
Standard nominal flow rate (standardised to DIN 1343)	261 l/min ... 1287 l/min
Nominal flow rate standardised according to ISO 8778	282.9 l/min ... 1395.1 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Nominal torque	9.5 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	57 g
Pneumatic connection, port 1	Male thread G1/4
Note on materials	RoHS-compliant
Material seals	NBR
Material spring	High-alloy stainless steel
Material housing	Brass, nickel-plated
Material thread seal	PA66-GF30/TPE-U
Material thread piece	Nickel-plated brass
Material of inner raceway	Brass
Material snap ring	High-alloy stainless steel
Material pins	High-alloy stainless steel
Valve body material	Brass
Material releasing sleeve	PP