

# Trunnion mounting kit DAMT-V1-32-A

Part number: 2213233

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	32
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	0.9 kN
Product weight	220 g
Note on materials	RoHS-compliant
Material screws	Steel Galvanised
Material trunnion flange	Galvanised steel
Material clamping piece	Galvanised steel
Material rod	High-alloy stainless steel