

Semi-rotary drive DRRD-8-180-FH-PA

Part number: 2223060

FESTO



 General operating condition

Data sheet

Feature	Value
Size	8
Cushioning angle	38 deg
Setting range of swivel angle for each end position	+10/-100 deg
Swivel angle	180 deg
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Design	Rack and pinion
Position detection	Via proximity switch
Symbol	00991265
Operating pressure	0.3 MPa ... 0.8 MPa
Operating pressure	3 bar ... 8 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	-10 °C ... 60 °C
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	0.2 Nm
Permissible mass moment of inertia	0.0015 kgm ²
Product weight	155 g
Type of mounting	With through-hole Via female thread
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material drive shaft	High-alloy stainless steel
Material seals	NBR TPE-U(PU)
Material housing	Smooth anodised