


# Axial kit EAMM-A-D60-60G-G2

Part number: 2256696

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal length	74.4 mm
Mounting position	optional
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	34.8 kgmm <sup>2</sup>
Transmittable torque	21 Nm
Product weight	1250 g
Interface code, actuator	D60 D60C
Interface code, motor in	60G
Note on materials	RoHS-compliant