

# Clamping sleeve EAMH-86-14-C27.3

Part number: 2429534

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	86
Mounting position	optional
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	9.9 kgmm <sup>2</sup>
Product weight	102 g
Note on materials	RoHS-compliant