

Clamping sleeve EAMH-86-19-C27.3

Part number: 2429535

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	86
Mounting position	optional
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	8.2 kgmm ²
Product weight	76 g
Note on materials	RoHS-compliant