


Axial kit EAMM-A-D100-120G

Part number: 2449341

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal length	113.5 mm
Mounting position	optional
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	280 kgmm ²
Transmittable torque	143 Nm
Product weight	3520 g
Interface code, actuator	D100
Interface code, motor in	120G
Note on materials	RoHS-compliant