

Sealing ring NPAS-C1-R-G14-P-FD-P10

Part number: 2652517

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size of pack	10
Mounting position	optional
Operating pressure complete temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Operating pressure complete temperature range	-13.775 psi ... 174 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) Water vapour
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B2-L
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C ... 120 °C
Nominal torque	20 Nm
Tolerance for nominal tightening torque	± 10%
Product weight	0.05 g
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material seals	PEEK