

Parallel kit EAMM-U-86-D50-60G-102

Part number: 2803125

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	86
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	175 kgmm ²
Frictional torque independent of load	0.25 Nm
Transmittable torque	9.5 Nm
Product weight	2510 g
Interface code, actuator	D50B
Interface code, motor in	60G
Note on materials	RoHS-compliant