

# Flange mounting EAHH-V2-32-R1

Part number: 2827587

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	32
Based on standard	ISO 15552
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Max. load capacity	1 kN
Product weight	206 g
Note on materials	RoHS-compliant
Material plate	High-alloy stainless steel
Material screws	High-alloy stainless steel