

Bellows kit EADB-V2-50-S401-500

Part number: 2828843

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--------------------------------|---|
| Outside diameter | 93 mm |
| Size | 50 |
| Stroke range | 401 mm ... 500 mm |
| Piston rod extension | 119 mm |
| Design | Round |
| Mounting position | optional |
| Design | With ducted exhaust air |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Media resistance | Dust Chips Oils Grease Petrol |
| Degree of protection | IP65 To IEC 60529 |
| Ambient temperature | -10 °C ... 80 °C |
| Moving mass | 305 g |
| Product weight | 402 g |
| Type of mounting | Push-on Via threaded pin |
| Pneumatic connection | G1/4 |
| Note on materials | RoHS-compliant |
| Material adapter components | Wrought aluminium alloy Anodised |
| Material seals | NBR |
| Material bellows | NBR |
| Material threaded pin | High-alloy stainless steel |