

Plug socket with cable KME-1-24-5-LED

Part number: 30945

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|---|
| Signal status display | Yellow LED |
| Type of mounting | On solenoid valve via M3 central screw |
| Mounting position | optional |
| Product weight | 280 g |
| Electrical connection 1 | Angled socket, square design, 3-pin, type C |
| Electrical connection 2 | Open end, 2-wire |
| Nominal operating voltage DC | 24 V |
| Current rating at 40° C | 4 A |
| Protective conductor connection | Not available |
| Cable length | 5 m |
| Cable characteristic | For static applications |
| Min. cable bending radius | 52 mm |
| Cable diameter | 5.2 mm |
| Cable diameter tolerance | ± 0.1 mm |
| Cable structure | 2 x 0.75 mm ² |
| Degree of protection | IP67 To IEC 60529 |
| Ambient temperature | -20 °C ... 80 °C |
| CE mark (see declaration of conformity) | In accordance with EU RoHS Directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| Material cable sheath | PVC |
| Material housing | TPE-U(PU) |
| Material seals | NBR |
| Material electrical contact | Silver-plated copper alloy |