

# Protective conduit fitting MKGV-23-M32-B

Part number: 3152612

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	optional
Size of pack	100
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP54
Ambient temperature	-40 °C ... 100 °C
Type of mounting	Via male thread
Note on materials	RoHS-compliant
Material fitting	PA