

# Clevis foot LSNG-63

Part number: 31743

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                         |
|--------------------------------|-------------------------------|
| Size                           | 63                            |
| Based on standard              | VDMA 24562                    |
| Corrosion resistance class CRC | 1 - Low corrosion stress      |
| LABS (PWIS) conformity         | VDMA24364-B2-L                |
| Ambient temperature            | -40 °C ... 150 °C             |
| Max. load capacity             | 4 kN                          |
| Product weight                 | 534 g                         |
| Note on materials              | RoHS compliant                |
| Material mounting              | Spheroidal graphite cast iron |
| Material rod end bearing       | Steel<br>PTFE                 |