

Right angle clevis foot LQG-32

Part number: 31768

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|--------------------------|
| Size | 32 |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -40 °C ... 150 °C |
| Max. load capacity | 0.9 kN |
| Product weight | 301 g |
| Product weight | 10.61 oz |
| Note on materials | RoHS compliant |
| Material mounting | Cast stainless steel |
| Material bolt | Case-hardened steel |
| Material lock | Spring steel |