

Clevis foot LNG-100

Part number: 33895

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|---|
| Size | 100 |
| Based on standard | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -40 °C ... 80 °C |
| Max. load capacity | 9 kN |
| Product weight | 1139 g |
| Note on materials | RoHS-compliant |
| Material mounting | Spheroidal graphite cast iron |
| Material bearing | PA |