# Guide unit
# FENG-32-200-KF

Part number: 34496

General operating condition

## Data sheet

| Feature | Value |
|---|---|
| Size | 32 |
| Stroke | 200 mm |
| Mounting position | optional |
| Guide | Recirculating ball bearing guide |
| Design | Guidance |
| Explosion protection | The information in the certificate must be observed! |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Max. force Fy | 750 N |
| Max. force Fy static | 1020 N |
| Max. force Fz | 750 N |
| Max. force Fz static | 1020 N |
| Max. moment Mx | 28 Nm |
| Max. torque Mx static | 38 Nm |
| Max. moment My | 34 Nm |
| Max. torque My static | 46 Nm |
| Max. moment Mz | 34 Nm |
| Max. torque Mz static | 46 Nm |
| Displacement force | 15 N |
| Product weight | 1890 g |
| Type of mounting | Via female thread |
| Note on materials | RoHS-compliant |
| Material guide component | Tempered steel |
| Material housing | Anodised wrought aluminium alloy |
| Material yoke plate | Anodised wrought aluminium alloy |