

Exhaust protection VABD-D3-SN-N12

Part number: 3535104

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	optional
Symbol	00991455
Operating pressure	0 MPa ... 1.2 MPa
Operating pressure	0 bar ... 12 bar
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:~:]
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Ambient temperature	-50 °C ... 60 °C
Type of mounting	Screw-in Via male thread
Note on materials	RoHS-compliant
Material seals	EPDM
Material vent screw	PA