

Check valve H-M5

Part number: 3671

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Type of mounting	In-line installation
Standard nominal flow rate (standardised to DIN 1343)	140 l/min
Operating pressure	0.04 MPa ... 0.8 MPa
Operating pressure	0.4 bar ... 8 bar
Ambient temperature	-10 °C ... 60 °C
Material housing	Brass
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Symbol	00991455
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B2-L
Media temperature	-10 °C ... 60 °C
Note on materials	RoHS-compliant
Material seals	NBR