

Connecting cable NHSB-A1-0,6-BLG3-LE3-PU8-2XBB

Part number: 3673475

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---------------------------------------|---|
| Protective conduit length | 0.6 m |
| Mounting position | optional |
| Outdoor applications | Weather-protected application areas Class C1 based on IEC 60654-1 |
| Operational voltage range DC | 0 V ... 30 V |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Relative air humidity | 5 - 100% Condensing |
| Degree of protection | IP65 IP67 IP69K NEMA 4 |
| Ambient temperature | -20 °C ... 60 °C |
| Ambient temperature with moving cable | -5 °C ... 60 °C |
| Electrical connection 1 | Straight plug connector, 3-pin |
| Electrical connection 2 | Open end, 3-wire |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible |
| Pneumatic connection | For tubing O.D. 8 mm |
| Min. cable bending radius | 100 mm |
| Cable structure | 3 x 0.75 mm ² |
| Product weight | 280 g |
| Note on materials | RoHS-compliant |
| Material conduit | PA |
| Material protective conduit fitting | PA |
| Material cable sheath | PVC |
| Material seals | TPE |