

Adaptive gripper finger DHAS-GF-120-U-BU

Part number: 3998959

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Size	120
Mounting position	optional
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Suitable for use with food	See supplementary material information
Ambient temperature	10 °C ... 50 °C
Product weight	29 g
Note on materials	RoHS-compliant
Material clamp jaws	TPE-U(PU)