

Position indicator SASF-S2-B-F-A34

Part number: 4046082

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Rotation angle adjustment range	0 deg ... 90 deg
Dimensions (W x L x H)	Diameter 65 x 40
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-25 °C ... 70 °C
Product weight	55 g
Type of mounting	To VDI/VDE 3845
Housing colour	Black
Note on materials	RoHS-compliant
Material spacer	PA
Material housing	PP High-alloy stainless steel
Material screws	High-alloy stainless steel