

Cable connector NETC-P-M12-EX4

Part number: 4197366

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Ambient temperature	-20 °C ... 70 °C
Degree of protection	IP66 IP68
Explosion ignition protection type for gas	Ex eb IIC Gb
Explosion ignition protection type for dust	Ex tb IIIC Db
Explosion ambient temperature	-20°C ≤ Ta ≤ +70°C
Explosion protection certification outside the EU	EPL Db (IEC-EX) EPL Gb (IECEX)
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX) In accordance with EU RoHS Directive
Size	M12x1.5
Cable diameter	4 mm ... 7 mm
Colour	Blue
Material cable gland	PA
Material seals	EPDM
Product weight	4 g
Size of pack	1
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	3 - high corrosion stress