

Cable connector NETC-P-M12

Part number: 4197367

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Ambient temperature	-20 °C ... 70 °C
Degree of protection	IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
Size	M12x1.5
Cable diameter	3 mm ... 6.5 mm
Colour	Black
Material cable gland	PA
Material seals	EPDM
Product weight	4 g
Size of pack	1
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	3 - high corrosion stress