

# Pressure indicator OH-22-GE

Part number: 4601

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Symbol	00991500
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 45 °C
Product weight	25 g
Pneumatic connection	G1/8
Note on materials	RoHS compliant