

# Coupling EAMD-21-15-12-8X10

Part number: 4820335

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting diameter 1	12 mm
Mounting diameter 2	8 mm
Size	21
Nominal length	15 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	0.45 kgmm <sup>2</sup>
Transmittable torque	2 Nm
Product weight	13.5 g
Note on materials	RoHS-compliant