

Flange mounting DAMF-Q12-25

Part number: 4965020

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	25
Mounting position	optional
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	4 Nm
Product weight	147 g
Type of mounting	With through-hole
Note on materials	RoHS-compliant
Material mounting	Galvanised steel
Material screws	Galvanised steel