

Coupling EAMD-67-51-22-32X32-U

Part number: 5070937

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Mounting diameter 1 | 22 mm |
| Mounting diameter 2 | 32 mm |
| Size | 67 |
| Nominal length | 51 mm |
| Mounting position | optional |
| Max. rotational speed | 4500 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -25 °C ... 60 °C |
| Mass moment of inertia | 374 kgmm ² |
| Transmittable torque | 133 Nm |
| Product weight | 740 g |
| Note on materials | RoHS-compliant |