

# Clevis foot LN-80

Part number: 5151

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	80
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Product weight	793 g
Note on materials	RoHS-compliant
Material mounting	Spheroidal graphite cast iron