

# Motor cable NEBM-M40G15-EH-20-Q11N-R3LEG14

Part number: 5251400

FESTO



 General operating condition

## Data sheet

Feature	Value
Based on standard	EN 61984
Cable designation	Without inscription label holder
Product weight	8220 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Hybrid socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M40x1
Electrical connection 1, number of connections/cores	15
Electrical connection 1, used connections/cores	12
Electrical connection 1, type of mounting	Snap-locking
Electrical connection 1, connection pattern	00997393
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Plugs and cables
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connector system	RJ45 and open end
Electrical connection 2, number of connections/cores	14
Electrical connection 2, used connections/cores	12
Operational voltage range DC	0 V ... 850 V
Operational voltage range AC	0 V ... 630 V
Current rating at 40° C	31.9 A
Immunity to surge	6 kV
Cable length	20 m
Cable characteristic	Suitable for energy chains
Test conditions cable	Test conditions on request
Bending radius, fixed cable	65.6 mm
Bending radius, moving cable	123 mm
Cable diameter	16.4 mm
Cable diameter tolerance	± 0.3 mm
Cable structure	4 x 4 mm <sup>2</sup> + 1 x (2 x 1.5 mm <sup>2</sup> ) + 1 x (2 x 0.24 mm <sup>2</sup> + 2 x 2 x 0.15 mm <sup>2</sup> )
Wire ends	Wire ferrule
Degree of protection	IP67
Note on degree of protection	Depending on connection block
Ambient temperature	-40 °C ... 90 °C
Ambient temperature with moving cable	-25 °C ... 80 °C

<b>Feature</b>	<b>Value</b>
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Free of halogen
Pollution degree	3
Corrosion resistance class CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Grey
Material insulating sheath	PP