

# Manifold MHA3-PR6-3-1/8

Part number: 525223

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Max. number of valve positions	6
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Mounting method for sub-base	With through-hole With H-rail
Mounting method for valve	Via female thread
Pneumatic connection, port 1/33	G1/4
Pneumatic connection, port 2	Female thread G1/8
Pneumatic connection, port 3/11	G1/4
Material sub-base	Wrought aluminium alloy