

Manifold MHA4-PR8-3-1/4

Part number: 525237

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. number of valve positions	8
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	1400 g
Mounting method for sub-base	With through-hole With H-rail
Mounting method for valve	Via female thread
Pneumatic connection, port 1/33	G3/8
Pneumatic connection, port 2	Female thread G1/4
Pneumatic connection, port 3/11	G3/8
Material sub-base	Wrought aluminium alloy