

Plastic tubing PAN-V0-10X1,25-RT

Part number: 525476

FESTO



 General operating condition

Data sheet

Feature	Value
Outside diameter	12 mm
Outside diameter for push-in fitting	10 mm
Flow-relevant bending radius	56 mm
Inside diameter	7.5 mm
Min. bending radius	34 mm
Tubing characteristics	Suitable for energy chains
Operating pressure complete temperature range	-0.095 MPa ... 0.3 MPa
Operating pressure complete temperature range	-0.95 bar ... 3 bar
Operating pressure complete temperature range	-13.775 psi ... 43.5 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1.2 MPa
Temperature-dependent operating pressure	-0.95 bar ... 12 bar
Temperature-dependent operating pressure	-13.775 psi ... 174 psi
Note on operating pressure	Mineral oil: max. 0.3 MPa at max. 90 °C Water: max. 0.3 MPa at max. 90 °C
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Mineral oil Water (liquid, ice-free)
Fire test material	UL94 V-0 (casing)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C ... 90 °C
Product weight according to length	0.088 kg/m
Pneumatic connection	For push-in connector O.D. 10 mm
Colour	Red
Shore hardness	A 72 +/-4 D 57 +/-3
Note on materials	RoHS-compliant
Material tubing	PA12-P PVC-P