

Mounting kit CRSMB-8-32/100

Part number: 525565

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	8
Design	For round cylinders
Mounting position	optional
For piston diameter	Ø32 - Ø100
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitable for use with food	See supplementary material information
Degree of protection	IP65 IP68 IP69K
Ambient temperature	-40 °C ... 90 °C
Product weight	3 g
Type of mounting	Bonded
Note on materials	RoHS-compliant
Material housing	TPE-U(PU)