

# Fine filter LFMB-3/4-D-MAXI-DA-A

Part number: 532835

FESTO



General operating condition

## Data sheet

Feature	Value
Series	D
Size	Maxi
Design	Fibre filter
Grade of filtration	1 µm
Condensate drain	Fully automatic
Symbol	00991544
Operating pressure	0.2 MPa ... 1.2 MPa
Operating pressure	2 bar ... 12 bar
Operating pressure	29 psi ... 174 psi
Operating medium	Compressed air to ISO 8573-1:2010 [6:4:4] Inert gas
Air purity class at output	Compressed air to ISO 8573-1:2010 [5:4:3] Inert gas
Max. standard flow rate for clean air class	2220 l/min
Min. standard flow rate for clean air class	750 l/min
Filter efficiency	99.99 %
Max. condensate volume	80 ml
Bowl guard	Metal bowl guard
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	1.5 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Storage temperature	-10 °C ... 60 °C
Filter efficiency, fine particles	99 %
Residual oil content	0.5 mg/m <sup>3</sup>
Filter efficiency, oil aerosol	90 %
Differential pressure display	Visual indicator
Type of mounting	With accessories
Mounting position	Vertical +/-5°
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 2	G3/4
Material housing	Die-cast zinc
Material filter	Borosilicate fibre

<b>Feature</b>	<b>Value</b>
Material bowl	Makrolon®
Note on materials	RoHS compliant
Product weight	1340 g