

Power supply socket NTSD-WD-11

Part number: 533119

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	Via union nut
Mounting position	optional
Product weight	34 g
Electrical connection	4-pin Angled socket Screw terminal
Operational voltage range AC	≤250 V
Permissible current load	16 A
Cable fitting	Pg11
Permissible cable diameter	5 mm ... 11 mm
Connection cross section	2.5 mm ²
Degree of protection	IP67
Ambient temperature	-5 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PBT
Material electrical contact	Copper alloy Brass