

Push-in T-fitting QBT-1/8-3/16-U-M

Part number: 533253

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 2.997 mm |
| Type of seal on screwed plug | Coating |
| Design | T-shape |
| Size of pack | 10 |
| Operating pressure complete temperature range | 0.095 MPa ... 1 MPa |
| Operating pressure complete temperature range | 0.95 bar ... 10 bar |
| Operating pressure complete temperature range | 13.775 psi ... 145 psi |
| Maritime classification | See certificate |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Ambient temperature | 0 °C ... 60 °C |
| Product weight | 12.814 g |
| Type of mounting | External hexagon, size 10 mm |
| Pneumatic connection, port 1 | Male thread R1/8 |
| Pneumatic connection, port 2 | For tubing outside diameter of 3/16" |
| Ambient temperature | 32 °F ... 140 °F |
| Colour of release ring | grey |
| Note on materials | RoHS-compliant |
| Material housing | PBT |
| Material thread seal | NBR |
| Material release ring | POM |
| Material tubing clamp component | High-alloy stainless steel |