

Sub-base CDSV5.0-AS-1/8

Part number: 534434

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. number of valve positions	1
Nominal operating voltage DC	24 V
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media temperature	-5 °C ... 50 °C
Sound pressure level	75 dB(A)
Degree of protection	IP65 IP66 IP67 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	690 g
Electrical connection	Cable
Type of mounting	With through-hole With female thread
Breather connection	M5
Pilot exhaust port 82/84	M5
Pilot air port 12	M5
Pilot air port 14	M5
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	G1/8
Pneumatic connection, port 4	G1/8
Pneumatic connection, port 5	G1/8
Note on materials	RoHS compliant