

Branching module MS4-FRM-1/4-I-Z

Part number: 536971

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	optional
Design	With non-return function
Symbol	00991511
Operating pressure	0 bar ... 10 bar
Standard nominal flow rate in main flow direction 1->2	1750 l/min
Standard nominal flow rate, outlet upwards	500 l/min
Standard nominal flow rate, outlet downwards	500 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gas
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Suitable for use with food	See supplementary material information
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	160 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 4	G1/4
Note on materials	RoHS-compliant
Material housing	Die-cast aluminium