


Transmitter SOEG-S-M18-K-L

Part number: 537691

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Symbol	00991642
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Measured variable	Position
Measuring principle	Optoelectronic
Measurement method	Through-beam sensor Transmitter
Type of light	Red
Operating distance	20000 mm
Ambient temperature	-25 °C ... 55 °C
Short circuit current rating	Pulsed
Operational voltage range DC	10 V ... 36 V
Residual ripple	20%
No-load supply current	15 mA
Reverse polarity protection	For all electrical connections
Electrical connection	Cable
Cable length	2.5 m
Material cable sheath	TPE-U(PUR)
Size	M18x1
Type of mounting	Via lock nut
Tightening torque	20 Nm
Product weight	115 g
Material housing	Chrome-plated
Material union nut	Brass Chrome-plated
Ambient temperature with moving cable	-5 °C ... 55 °C
Degree of protection	IP65 IP67
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L