

Swivel flange SNCL-16-R3

Part number: 537795

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|--|
| Size | 16 |
| Based on standard | ISO 21287 |
| Variants | High corrosion protection |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -40 °C ... 90 °C |
| Product weight | 21 g |
| Note on materials | RoHS-compliant |
| Material mounting | Wrought aluminium alloy With protective coating |
| Material bearing | Polymer |
| Material screws | High-alloy stainless steel |