

# Electronics module VMPA2-FB-EMG-4

Part number: 537984

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Diagnosis	Undervoltage of valves
Max. number of valve positions	2
Max. number of valve coils	4
Internal current consumption, load voltage	23 mA
Internal current consumption, operating voltage	8 mA
Nominal pick-up current per solenoid coil	99 mA up to 24 ms
Nominal current with current reduction	18 mA after 24 ms
Corrosion resistance class CRC	(when installed)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	20 g
Material housing	POM
Note on materials	RoHS-compliant