

Electrical module VMPA2-MPM-EMM-2

Part number: 537985

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. number of valve positions	2
Max. number of valve coils	2
Nominal pick-up current per solenoid coil	100 mA up to 30 ms
Nominal current with current reduction	20 mA after 30 ms
Corrosion resistance class CRC	(when installed)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	20 g
Material housing	POM
Note on materials	RoHS-compliant